



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> min.
14 .55	M 5	7 .28	34 1.34	25 .98
23 .91	M 6	14 .55	60 2.36	17 .67
23 .91	M 8	14 .55	60 2.36	22 .87
26 1.02	M 8	16 .63	70 2.76	25 .98
26 1.02	M 10	16 .63	70 2.76	25 .98
30 1.18	M 10	16 .63	65 2.56	26 1.02
30 1.18	M 12	16 .63	65 2.56	26 1.02
35 1.38	M 12	22 .87	85 3.35	25 .98
35 1.38	M 16	22 .87	85 3.35	25 .98

**Specification**

- Plastic  
Duroplast (Phenolic PF)
  - Temperature resistant up to 230 °F (110 °C)
  - Black, glossy finish
  - Molded-in thread

• RoHS compliant

**Information**

GN 201 elliptical shaped knobs are often used on GN 310 gear lever handles instead of DIN 319 ball knobs.

How to order <sup>1</sup> <sup>2</sup> <b>GN201-30-M10</b>	<b>1</b> Handle diameter d <sub>1</sub>
	<b>2</b> Thread d <sub>2</sub>