



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	d ₃	l ₁	l ₂ min.
14 .55	M 5	7 .28	34 1.34	25 .98
23 .91	M 6	14 .55	60 2.36	17 .67
23 .91	M 8	14 .55	60 2.36	22 .87
26 1.02	M 8	16 .63	70 2.76	25 .98
26 1.02	M 10	16 .63	70 2.76	25 .98
30 1.18	M 10	16 .63	65 2.56	26 1.02
30 1.18	M 12	16 .63	65 2.56	26 1.02
35 1.38	M 12	22 .87	85 3.35	25 .98
35 1.38	M 16	22 .87	85 3.35	25 .98

Specification

- Plastic
Duroplast (Phenolic PF)
 - Temperature resistant up to 230 °F (110 °C)
 - Black, glossy finish
 - Molded-in thread

• RoHS compliant

Information

When using GN 201 elliptical shaped knobs, it must be ensured that the threaded stud is not too short. Otherwise, there is a risk that the Duroplast plastic body could break under certain loads.

These knobs are often used on GN 310 gear lever handles instead of DIN 319 ball knobs.

How to order ¹ ² GN 201-30-M10	1 Handle diameter d ₁
	2 Thread d ₂