



Metric table

Dimensions in: millimeters - *inches*

¹ d_1	² d_2 Thread	d_3	l_1	l_2
12 .47	M 4	9 .35	40 1.57	8 .31
15 .59	M 5	11 .43	50 1.97	7 .28
18 .71	M 6	13 .51	64 2.52	8 .31
21 .83	M 6	15 .59	72 2.83	10 .39
21 .83	M 8	15 .59	72 2.83	10 .39
25 .98	M 8	17 .67	90 3.54	10 .39
26 1.02	M 10	20 .79	100 3.94	12 .47
33 1.30	M 12	25 .98	124 4.88	14 .55

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, glossy finish
- Threaded stud
Steel, zinc plated, blue passivated finish, molded-in
- RoHS compliant

Information

GN 203 tapered handles are used in applications where a positive non-revolving grip is required. They are not suitable for applications where the handle is exposed to heavy loads. For applications with increased loads, see EN 539 cylindrical handles.

see also...

- Fixed Cylindrical Handles EN 539

How to order ¹ ² GN 203-21-M6	1 Handle diameter d_1
	2 Thread d_2