



**Metric table**

Dimensions in: millimeters - *inches*

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$ Thread	$d_3$	$l_1$	$l_2$
12 .47	M 4	9 .35	40 1.57	8 .31
15 .59	M 5	11 .43	50 1.97	7 .28
18 .71	M 6	13 .51	64 2.52	8 .31
21 .83	M 6	15 .59	72 2.83	10 .39
21 .83	M 8	15 .59	72 2.83	10 .39
25 .98	M 8	17 .67	90 3.54	10 .39
26 1.02	M 10	20 .79	100 3.94	12 .47
33 1.30	M 12	25 .98	124 4.88	14 .55

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, glossy finish
- Threaded stud  
Steel, zinc plated, blue passivated finish, molded-in
- RoHS compliant

**Information**

GN 203 tapered handles are used in applications where a positive non-revolving grip is required. They are not suitable for applications where the handle is exposed to heavy loads. For applications with increased loads, see EN 539 cylindrical handles.

How to order <sup>1</sup> <sup>2</sup> <b>GN 203-21-M6</b>	<b>1</b> Handle diameter $d_1$
	<b>2</b> Thread $d_2$