



Metric table

Dimensions in: millimeters - inches

| ¹ d ₁ | ² d ₂ Thread | | d ₃ ≈ | h | t min. |
|--------------------------------|--|------|------------------|------------|-----------|
| 20 .79 | M 5 | M 6 | 12 .47 | 30 1.18 | 18 .71 |
| 25 .98 | M 6 | M 8 | 15 .59 | 38 1.50 | 18 .71 |
| 30 1.18 | M 8 | M 10 | 18 .71 | 46 1.81 | 18 .71 |
| 35 1.38 | M 10 | M 12 | 21 .83 | 53 2.09 | 21 .83 |

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, glossy finish
- Molded-in thread

• RoHS compliant

Information

GN 419 tapered knobs series are often used on gear lever handles instead of DIN 319 ball knobs series. They feature a modern and streamlined shape.

| | |
|---|---|
| <p>How to order</p> <p>¹ ²</p> <p>GN 419-25-M8</p> | 1 Handle diameter d ₁ |
| | 2 Thread d ₂ |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

