



3 Type
A With DIN 912 socket cap screw
B With adjustable lever

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Clamping Ø	d ₃ Thread	l ₁	l ₂	l ₃	l ₄	l ₅	m
28 1.10	8 .31	M 6	33 1.30	35 1.38	45 1.77	14 .55	5 .20	13 .51
32 1.26	10 .39	M 8	45 1.77	45 1.77	63 2.48	20 .79	5 .20	15 .59
36 1.42	12 .47	M 8	47 1.85	45 1.77	63 2.48	21 .83	5 .20	17 .67
46 1.81	16 .63	M 10	57 2.24	55 2.17	78 3.07	25.5 1.00	6 .24	22 .87

Specification

- Aluminum
 - Plain, matte tumbled finish ● MT
 - Powder coated Black, RAL 9005, textured finish ● SW
- Socket cap screws DIN 912
 - Stainless steel
 - European Standard No. 1.4301 (AISI 304)
- Hexagon nuts DIN 934
 - Stainless steel
 - European Standard No. 1.4301 (AISI 304)
- Adjustable lever
 - Zinc die casting, plastic coated
 - Silver, RAL 9006, textured finish
 - Insert, screw, spring and distance bushing
 - Stainless steel
 - European Standard No. 1.4305 (AISI 303)
- RoHS compliant

Information

GN 490 adjustable two-way clamping joints clamp rods or tubes via a V-groove, allowing a greater Ø tolerance to be bridged.

The pressure spring makes clamping and releasing easier.

see also...

- Range of Clamp Mountings
- Two-Way Connector Mini Clamps GN 474
- Adjustable Two-Way Connector Mini Clamps GN 475
- Two-Way Base Connector Mini-Clamps GN 473
- Solid Round Shafting and Hollow Round Tubings GN 480.1

How to order	
1 Diameter d ₁	
2 Clamping diameter d ₂	
3 Type	
4 Finish	

GN 490-32-10-B-MT