



ELESA original design EBS+x



Metric table

Dimensions in: millimeters - inches

¹ d ₁ Handle diameter	² d ₂ Thread	d ₃	d ₄ +0.5	l ₁	l ₂	l ₃ ≈	l ₄ ≈
45 1.77	M 10	12 .47	32 1.26	64 2.52	17 .67	1 .04	22 .87

Specification

- Plastic
Technopolymer (Polypropylene PP)
- Temperature resistant up to 175 °F (80 °C)
- Black, matte finish
- Threaded stud
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

EN 596 revolving ball knobs are used in applications that require friction-free turning action, such as vertically positioned handwheels or cranked handles.

see also...

- Product Range Ergostyle®
- Softline Revolving Mushroom Shaped Knobs EN 597.1

How to order

¹ ²
EN 596-45-M10

1 Handle diameter d₁

2 Thread d₂