



**Inch table**

Dimensions in: inches - millimeters

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>
	Plastic KU	KT					
.71 18	1/4 x 20	1/4 x 20	.39 10	.59 15	1.57 40	.47 12	.10 2.5
.83 21	1/4 x 20	1/4 x 20	.39 10	.67 17	1.97 50	.51 13	.10 2.5
.91 23	5/16 x 18	5/16 x 18	.51 13	.75 19	2.56 65	.55 14	.10 2.5
1.02 26	3/8 x 16	3/8 x 16	.51 13	.83 21	3.15 80	.63 16	.10 2.5
1.10 28	3/8 x 16	3/8 x 16	.51 13	.87 22	3.54 90	.63 16	.10 2.5
1.22 31	1/2 x 13	-	.55 14	.98 25	4.02 102	.79 20	.10 2.5

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>				d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>
	Plastic KU	KT	Steel ST						
14 .55	-	-	M 6	-	8 .31	11 .43	28 1.10	10 .39	.5 .02
18 .71	M 6	-	M 6	-	10 .39	15 .59	40 1.57	12 .47	2.5 .10
21 .83	M 6	M 8	M 6	M 8	10 .39	17 .67	50 1.97	13 .51	2.5 .10
22 .87	M 6	M 8	M 6	M 8	10 .39	18 .71	56 2.20	13 .51	2.5 .10
23 .91	M 8	M 10	M 8	M 10	13 .51	19 .75	65 2.56	14 .55	2.5 .10
26 1.02	M 8	M 10	M 8	M 10	13 .51	21 .83	80 3.15	16 .63	2.5 .10
28 1.10	M 10	-	M 10	-	13 .51	22 .87	90 3.54	16 .63	2.5 .10
31 1.22	M 12	-	-	-	14 .55	25 .98	102 4.02	20 .79	2.5 .10

**Specification**

- Plastic **KU**  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, smooth glossy finish
- Plastic **KT**  
Technopolymer (Polypropylene PP)  
- Temperature resistant up to 176 °F (80 °C)  
- Black, smooth matte finish  
- Black, smooth glossy finish (only size 14)
- Steel **ST**  
Powder coated black, matte textured finish
- Threaded spindle  
Steel zinc plated, blue passivated finish
- RoHS compliant

**Information**

GN 598 cylindrical revolving handles are noted for their modern design, and they blend in well with rectangular shaped rim handwheels.

Steel handles are mainly used on safety clutch handwheels to increase imbalance and thus avoid free wheeling.

see also...

- Fixed Cylindrical Handles EN 539
- Retractable Handles GN 598.3 (with Locking Mechanism)

How to order <b>GN 598-KU-31-1/2X13</b>	1	Material
	2	Handle diameter d <sub>1</sub>
	3	Thread d <sub>2</sub>