



Inch table

Dimensions in: inches - millimeters

d ₁	d ₂		d ₃	d ₄	l ₁	l ₂	l ₃
	Plastic KU	KT					
.71 18	1/4 x 20	1/4 x 20	.39 10	.59 15	1.57 40	.47 12	.10 2.5
.83 21	1/4 x 20	1/4 x 20	.39 10	.67 17	1.97 50	.51 13	.10 2.5
.91 23	5/16 x 18	5/16 x 18	.51 13	.75 19	2.56 65	.55 14	.10 2.5
1.02 26	3/8 x 16	3/8 x 16	.51 13	.83 21	3.15 80	.63 16	.10 2.5
1.10 28	3/8 x 16	3/8 x 16	.51 13	.87 22	3.54 90	.63 16	.10 2.5
1.22 31	1/2 x 13	-	.55 14	.98 25	4.02 102	.79 20	.10 2.5

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂				d ₃	d ₄	l ₁	l ₂	l ₃
	Plastic KU	KT	Steel ST						
14 .55	-	-	M 6	-	8 .31	11 .43	28 1.10	10 .39	.5 .02
18 .71	M 6	-	M 6	-	10 .39	15 .59	40 1.57	12 .47	2.5 .10
21 .83	M 6	M 8	M 6	M 8	10 .39	17 .67	50 1.97	13 .51	2.5 .10
22 .87	M 6	M 8	M 6	M 8	10 .39	18 .71	56 2.20	13 .51	2.5 .10
23 .91	M 8	M 10	M 8	M 10	13 .51	19 .75	65 2.56	14 .55	2.5 .10
26 1.02	M 8	M 10	M 8	M 10	13 .51	21 .83	80 3.15	16 .63	2.5 .10
28 1.10	M 10	-	M 10	-	13 .51	22 .87	90 3.54	16 .63	2.5 .10
31 1.22	M 12	-	-	-	14 .55	25 .98	102 4.02	20 .79	2.5 .10

Specification

- Plastic **KU**
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, glossy finish
- Plastic **KT**
Technopolymer (Polypropylene PP)
- Temperature resistant up to 176 °F (80 °C)
- Black, matte finish
- Black, glossy finish (only size 14)
- Steel **ST**
Powder coated black, matte textured finish
- Threaded spindle
Steel zinc plated, blue passivated finish
- RoHS compliant

Information

GN 598 revolving handles are noted for their modern design, and they blend in well with rectangular shaped rim handwheels.

Steel handles are mainly used on safety clutch handwheels to increase imbalance and thus avoid free wheeling.

see also...

- Fixed Cylindrical Handles EN 539
- Retractable Handles GN 598.3 (with Locking Mechanism)

How to order (Inch)	1 Material
GN 598-KU-31-1/2X13	2 Handle diameter d ₁
	3 Thread d ₂

How to order (Metric)	1 Material
GN 598-KT-21-M8	2 Handle diameter d ₁
	3 Thread d ₂