



**SS** Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

<sup>2</sup> d <sub>1</sub>	<sup>3</sup> d <sub>2</sub>		d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>
	KU	KT					
18 .71	M 6	M 6	10 .39	15 .59	40 1.57	12 .47	2.5 .10
21 .83	M 6	M 6	10 .39	17 .67	50 1.97	13 .51	2.5 .10
23 .91	M 8	M 8	13 .51	19 .75	65 2.56	14 .55	2.5 .10
26 1.02	M 10	M 10	13 .51	21 .83	80 3.15	16 .63	2.5 .10
28 1.10	M 10	M 10	13 .51	22 .87	90 3.54	16 .63	2.5 .10
31 1.22	M 12	-	14 .55	25 .98	102 4.02	20 .79	2.5 .10

**Specification**

- Plastic **KU**  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, smooth glossy finish
- Plastic **KT**  
Technopolymer (Polypropylene PP)  
- Temperature resistant up to 176 °F (80 °C)  
- Black, smooth matte finish
- Spindle  
Stainless steel  
European Standard No. 1.4305 (AISI 303)
- RoHS compliant

**Information**

- GN 598.1 revolving handles are noted for their modern design, and they blend in well with the rectangular shaped rim handwheels.
- see also...
- Retractable Handles GN 598.5 (with Locking Mechanism)
  - Revolving Handles EN 598.2

<p>How to order</p> <p><sup>1</sup> <sup>2</sup> <sup>3</sup></p> <p><b>GN 598.1-KU-26-M10</b></p>	<b>1</b> Material
	<b>2</b> Handle diameter d <sub>1</sub>
	<b>3</b> Thread d <sub>2</sub>