



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>		d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub> ≈	l <sub>5</sub>
GN 598.3	GN 598.5	Thread						
18 .71	-	M 5	16 .63	57 2.24	15 .59	5 .20	52 2.05	9.5 .37
21 .83	-	M 5	16 .63	67 2.64	15 .59	5 .20	62 2.44	9.5 .37
22 .87	-	M 5	16 .63	73 2.87	15 .59	5 .20	68 2.68	9.5 .37
23 .91	23 .91	M 6	20 .79	87 3.43	19.5 .77	6 .24	80 3.15	10.5 .41
26 1.02	26 1.02	M 6	20 .79	102 4.02	19.5 .77	6 .24	95 3.74	10.5 .41
28 1.10	28 1.10	M 8	26 1.02	118 4.65	26 1.02	10 .39	106 4.17	16 .63

**Specification**

- Handle  
Plastic **KU**  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, smooth glossy finish  
- Revolving  
- Handle holds in both positions
- **GN 598.3**  
Retractable mechanism  
Steel, blackened finish
- **GN 598.5**  
Retractable mechanism  
Stainless steel  
- Stem, retaining pin  
European Standard No. 1.4305 (AISI 303)  
- Hub  
Sintered steel  
European Standard No. 1.4404 (AISI 316 LHC)
- RoHS compliant

**Information**

GN 598.3 and GN 598.5 retractable handles are suitable when the handle must be withdrawn during automatic operation.

The handle is pulled out of its tapered seat in the direction of the arrow and then tilted. A compression spring locks the handle in both end positions. A positive lock is achieved in the operating position by way of a tapered seat located in the hub of the mechanism.

see also...

- Safety Retractable Handles GN 798.7 (Automatic Fold-Down Type, Steel)
- Safety Retractable Handles GN 798.8 (Automatic Fold-Down Type, Stainless Steel)

**On request**

- Technopolymer plastic hand piece

How to order (Steel)	1 Material
<b>GN 598.3-KU-26</b>	2 Handle diameter d <sub>1</sub>

How to order (Stainless steel)	1 Material
<b>GN 598.5-KU-23</b>	2 Handle diameter d <sub>1</sub>