



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>		d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub> ≈	l <sub>5</sub>
GN 598.3	GN 598.5	Thread						
18	-	M 5	16	57	15	5	52	9.5
.71	-		.63	2.24	.59	.20	2.05	.37
21	-	M 5	16	67	15	5	62	9.5
.83	-		.63	2.64	.59	.20	2.44	.37
22	-	M 5	16	73	15	5	68	9.5
.87	-		.63	2.87	.59	.20	2.68	.37
23	23	M 6	20	87	19.5	6	80	10.5
.91	.91		.79	3.43	.77	.24	3.15	.41
26	26	M 6	20	102	19.5	6	95	10.5
1.02	1.02		.79	4.02	.77	.24	3.74	.41
28	28	M 8	26	118	26	10	106	16
1.10	1.10		1.02	4.65	1.02	.39	4.17	.63

**Specification**

- Handle Plastic Duroplast (Phenolic PF)
  - Temperature resistant up to 230 °F (110 °C)
  - Black, glossy finish
  - Revolving
  - Handle holds in both positions
- **GN 598.3** Retractable mechanism Steel, blackened finish
- **GN 598.5** Retractable mechanism Stainless steel
  - Stem, retaining pin European Standard No. 1.4305 (AISI 303)
  - Hub Sintered steel European Standard No. 1.4404 (AISI 316 LHC)
- RoHS compliant

**On request**

- Technopolymer plastic hand piece

**Information**

GN 598.3 and GN 598.5 retractable handles are suitable when the handle must be withdrawn during automatic operation.

The handle is pulled out of its tapered seat in the direction of the arrow and then tilted. A compression spring locks the handle in both end positions. A positive lock is achieved in the operating position by way of a tapered seat located in the hub of the mechanism.

see also...

- Safety Retractable Handles GN 798.7 (Automatic Fold-Down Type, Steel)
- Safety Retractable Handles GN 798.8 (Automatic Fold-Down Type, Stainless Steel)

How to order (Steel)	1	Material
	2	Handle diameter d <sub>1</sub>
<b>GN 598.3-KU-26</b>		

How to order (Stainless steel)	1	Material
	2	Handle diameter d <sub>1</sub>
<b>GN 598.5-KU-23</b>		