



SS Stainless Steel

### Metric table

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	<sup>3</sup> l <sub>1</sub>	d <sub>3</sub>	l <sub>2</sub>
13 .51	M 6	9 .35	8 .31	18 .71
14 .55	M 6	9 .35	8 .31	20 .79
16 .63	M 6	9 .35	8 .31	23 .91

### Specification

- Plastic  
Technopolymer (Polyamide PA)  
- Temperature resistant up to 176 °F (80 °C)  
- Black, smooth matte finish
- Spindle  
Stainless steel  
European Standard No. 1.4305 (AISI 303)
- RoHS compliant

### Information

GN 599.5 cylindrical revolving handles are mainly used on small handwheels (GN 736, GN 736.1) which are installed for control purposes where low torque is required (fingertip grip).

see also...

- Knurled Control Knobs GN 736
- Knurled Control Knobs with Disposition for Scale GN 736.1

How to order <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>GN 599.5-14-M6-9</b>	<b>1</b> Handle diameter d <sub>1</sub>
	<b>2</b> Thread d <sub>2</sub>
	<b>3</b> Length l <sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

