



ELESA original design ESP.



2 Type

- A Fixing with hexagon head screw
- B Fixing with countersunk screw

Universal table



Dimensions in: millimeters - inches

l_1	$l_2 \pm 0.5$	l_3	b_1	b_2	d	h_1	h_2	h_3	h_4	t
114 4.49	93.5 3.68	74 2.91	35 1.38	19 .75	6.5 .26	33 1.30	7 .28	11 .43	9 .35	5 .20

Specification



- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- Black-gray, matte finish, similar to RAL 7021
- Color of the cover (shiny finish):

● DSG	Black-gray, RAL 7021
● DOR	Orange, RAL 2004
● DGR	Gray, RAL 7035
● DGB	Yellow, RAL 1021
● DBL	Blue, RAL 5024
● DRT	Red, RAL 3000
- Mounting holes
Counterbored for inch or metric size screws
- Both dimensions, inch and metric, are interchangeable
- RoHS compliant

Information

When using guards on machines and automation systems, which include double hinged doors, the EN 630 Ergostyle® off-set “U” handle completely enclosed is a safety element for operator fingers while the doors are being used. Use of a colored safety cover makes identification easier.

Resistant to solvents, oils, grease and other chemical agents.

The cover is included but supplied unassembled.

see also...

- Product Range Ergostyle®
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems)
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems)

How to order	1 Length l_1
EN 630-114-B-DOR	2 Type
	3 Color of the cover