



ELESA original design EWP.



**2 Type**

- A** Fixing with hexagon head screw
- B** Fixing with countersunk screw

**Universal table**



Dimensions in: millimeters - inches

$l_1$	$l_2 \pm 0.5$	$l_3$	$b_1$	$b_2$	$d$	$h_1$	$h_2$	$h_3$	$h_4$	$t$
114 4.49	93.5 3.68	74 2.91	35 1.38	19 .75	6.5 .26	33 1.30	7 .28	11 .43	9 .35	5 .20

**Specification**



- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 230 °F (110 °C)  
- Black-gray, matte finish, similar to RAL 7021
- Color of the covers (shiny finish):
 

● DSG	Black-gray, RAL 7021
● DOR	Orange, RAL 2004
● DGR	Gray, RAL 7035
● DGB	Yellow, RAL 1021
● DBL	Blue, RAL 5024
● DRT	Red, RAL 3000
- Mounting holes  
Counterbored for inch or metric size screws
- Both dimensions, inch and metric, are interchangeable
- RoHS compliant

**Information**

When using guards on machines and automation systems, which include double hinged doors, use of colored covers makes identification of the EN 630.1 Ergostyle® off-set open “U” handle easier.  
Resistant to solvents, oils, grease and other chemical agents.  
The covers are included but supplied unassembled.

see also...

- Product Range Ergostyle®
- Cabinet “U” Handles GN 565.2  
(Aluminum, Angled, Mounting from the Back or from the Operator’s Side)
- Cabinet “U” Handles GN 425.1 (Offset)
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems)
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems)

How to order  <b>EN 630.1-114-A-DOR</b>	<b>1</b> Length $l_1$
	<b>2</b> Type
	<b>3</b> Color of the covers