



SS Stainless Steel

**3 Type**

- A Without knurl
- B With knurl

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Thread		d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
21 .83	M 4	M 5	12.5 .49	18 .71	10.5 .41	10
25 .98	M 6	M 8	14.5 .57	22.5 .89	14 .55	12
31 1.22	M 8	-	18.5 .73	27 1.06	17 .67	15
31 1.22	M 10	-	18.5 .73	27 1.06	17 .67	17

**Specification**

- **GN 676.1**  
Steel, black oxide finish
- **GN 676.5**  
Stainless steel
  - European Standard No. 1.4305 (AISI 303)
  - Matte shot-blasted finish
- **RoHS compliant**

**Information**

GN 676.1 and GN 676.5 knobs are used in applications where a push or pull movement is required. Their concave top gives a more comfortable thumb grip.

The attractively shaped knurled version (Type B) is supplied with a tapped blind hole.

see also...

- *Ergostyle® Knurled Knobs EN 676*
- *Waist Shaped Knobs GN 75*
- *Waist Shaped Knobs GN 75.5*

How to order (Steel) <b>GN 676.1-21-M5-B</b>	<b>1</b>	Handle diameter d <sub>1</sub>
	<b>2</b>	Thread d <sub>2</sub>
	<b>3</b>	Type
How to order (Stainless steel) <b>GN 676.5-31-M10-A</b>	<b>1</b>	Handle diameter d <sub>1</sub>
	<b>2</b>	Thread d <sub>2</sub>
	<b>3</b>	Type