



elesa

ELESA original design EKK-p



Dimensions in: inches - millimeters

Inch table

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	<sup>3</sup> Length l	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>
.83 21	10 x 32	.75 19	.49 12.5	.71 18	.41 10.5
.98 25	1/4 x 20	.75 19	.57 14.5	.89 22.5	.55 14
1.22 31	5/16 x 18	.75 19	.73 18.5	1.06 27	.67 17

Metric table

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	<sup>3</sup> Length l	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>			
16 .63	M 3	10 .39	16 .63	-	-	8.5 .33	13 .51	8.5 .33
18 .71	M 4	10 .39	16 .63	-	-	10.5 .41	15.5 .61	10.5 .41
21 .83	M 5	10 .39	16 .63	20 .79	-	12.5 .49	18 .71	10.5 .41
21 .83	M 6	16 .63	20 .79	30 1.18	-	12.5 .49	18 .71	10.5 .41
25 .98	M 6	16 .63	20 .79	25 .98	30 1.18	14.5 .57	22.5 .89	14 .55
25 .98	M 8	20 .79	25 .98	30 1.18	40 1.57	14.5 .57	22.5 .89	14 .55
31 1.22	M 8	20 .79	25 .98	30 1.18	40 1.57	18.5 .73	27 1.06	17 .67
31 1.22	M 10	30 1.18	40 1.57	-	-	18.5 .73	27 1.06	17 .67

Specification

- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)
- Color (matte finish):  
Black-gray, RAL 7021 ● SG
- Threaded stud  
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

When used as a push-pull button, the thumb rests naturally on the concave front surface, making it easier to grip the EN 676 Ergostyle® knurled knob. The slight knurling on the rim of the knob makes tightening or clamping operations easier.

Resistant to solvents, oils, grease and other chemical agents.

How to order (Inch)	<sup>1</sup> Handle diameter d <sub>1</sub>
	<sup>2</sup> Thread d <sub>2</sub>
	<sup>3</sup> Stud length l
	<sup>4</sup> Color
<b>EN 676-21-10X32-19-SG</b>	

How to order (Metric)	<sup>1</sup> Handle diameter d <sub>1</sub>
	<sup>2</sup> Thread d <sub>2</sub>
	<sup>3</sup> Stud length l
	<sup>4</sup> Color
<b>EN 676-31-M8-25-SG</b>	