



ELESA original design 1.222

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread		d ₃	h	t ₁ min.	t ₂ ±0.5
15 .59	M 6	-	12 .47	25 .98	16 .63	3.5 .14
20 .79	M 8	-	14 .55	31 1.22	20 .79	3.5 .14
26 1.02	M 8	M 10	17 .67	42 1.65	20 .79	5 .20
33 1.30	M 10	M 12	20 .79	54 2.13	40 1.57	8 .31
38 1.50	M 12	-	23 .91	68 2.68	45 1.77	11 .43
41 1.61	M 14	M 16	25 .98	87 3.43	55 2.17	14 .55

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- Molded-in thread

- RoHS compliant

Information

EN 719 domed gear lever knobs are very often used in place of ball knobs DIN 319 on switch levers, gear levers etc. Knobs for such applications are often chosen for ergonomical reasons.

see also...

- *Domed Gear Lever Knobs EN 719.2 (Tapped or Press-On Type)*

How to order ¹ ² EN 719-20-M8	1 Handle diameter d ₁
	2 Thread d ₂