



ELESA original design M.643-FM

Universal table

Dimensions in: millimeters - inches

Length l	a	b	d	h₁	h₂	t
86 ±0.5 3.39 ±0.02	14 .55	23 .91	5.4 .21	44 1.73	15 .59	5.5 .22
117 ±0.5 4.61 ±0.02	16 .63	25 .98	6.4 .25	49 1.93	15 .59	6 .24
132 ±1 5.20 ±0.04	16 .63	26 1.02	6.4 .25	53 2.09	15 .59	8.5 .33
179 ±1 7.05 ±0.04	16 .63	27 1.06	6.4 .25	57 2.24	15 .59	6 .24

Specification

- Plastic
Technopolymer (Polypropylene PP)
- Shock resistant
- Temperature resistant up to 212 °F (100 °C)
- Black, matte finish
- Tapped inserts
Brass, molded-in
- Mounting holes
Counterbored for inch or metric size socket cap screws
- Both dimensions, inch and metric, are interchangeable
- **RoHS compliant**

Information

EN 725.1 cabinet “U” handles are well known for their smooth ergonomically shaped elliptical design.
High impact strength.
Resistant to solvents, oils, grease and other chemical agents.

see also...

- Cabinet “U” Handles GN 565.1 (Aluminum)
- Cabinet “U” Handles GN 565.5 (Stainless Steel, Mounting from the Back or from the Operator’s Side)

On request

- Various metric and inch size fasteners and kit packaging

How to order	1 Length l
EN 725.1-179	