



SS Stainless Steel

3 Type

- D** With tapped hole
- E** With threaded stud

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Type D	2 d ₃ Type E	d ₄	h	Length l	t min.
16 .63	M 5	M 6	10 .39	18 .71	10 .39	7 .28
20 .79	M 6	M 8	12 .47	24 .94	12 .47	9 .35
25 .98	M 6	M 8	14 .55	29 1.14	14 .55	9 .35
32 1.26	M 8	M 10	18 .71	37 1.46	16 .63	12 .47
36 1.42	M 10	M 12	20 .79	42 1.65	18 .71	15 .59

* Not available from stock, requires a minimum order quantity

Specification

- **GN 75**
Steel
 - Fine turned
 - Black oxide finish
 - Machined from solid bar
- **GN 75.5**
Stainless steel
 - European Standard No. 1.4301 (AISI 304)
 - Matte shot-blasted finish **MT**
 - Highly polished finish **PL***
- **RoHS compliant**

Information

GN 75 waist shaped knobs are widely used on push / pull type applications. The smooth shape gives the operator a comfortable grip.

GN 75.5 waist shaped knobs are made of high-grade stainless steel, which makes them the first choice when it comes to applications requiring high standards of hygiene. The design of these knobs prevents the collection of moisture and dirt.

see also...

- *Push / Pull Knobs GN 676.1 (Steel, Black Oxide Finish)*
- *Push / Pull Knobs GN 676.5 (Stainless Steel)*

On request

- Steel, zinc plated finish
- Stainless steel A4 quality

How to order (Steel)	1 Handle diameter d ₁
1 2 3 GN 75-25-M6-D	2 Thread d ₂ (Threaded stud d ₃)
	3 Type

How to order (Stainless steel)	1 Handle diameter d ₁
1 2 3 4 GN 75.5-25-M8-E-MT	2 Thread d ₂ (Threaded stud d ₃)
	3 Type
	4 Finish