



- 3 Type**  
**D** With tapped hole  
**E** With threaded stud

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Type D	<b>2</b> d <sub>3</sub> Type E	d <sub>4</sub>	d <sub>5</sub>	h	Length l	t min.
20 .79	M 5	M 5	14 .55	14.8 .58	24 .94	10 .39	7 .28
25 .98	M 6	M 6	16 .63	16.8 .66	29 1.14	12 .47	9 .35
32 1.26	M 8	M 8	18 .71	18.8 .74	37 1.46	14 .55	12 .47

**Specification**

- Stainless steel  
European Standard No. 1.4404, A4 (AISI 316L)  
- Matte finish (Ra < 0.8 µm) **MT**  
- Polished finish (Ra < 0.8 µm) **PL**
- Sealing ring  
Hydrogenated acrylonitrile butadiene rubber (H-NBR)  
- Blue  
- Temperature resistant from -13 °F to 302 °F (-25 °C to +150 °C)  
- Hardness 85 ±5 shore A  
- FDA compliant
- RoHS compliant

**Information**

GN 75.6 waist shaped knobs are intended for use in hygiene areas. The sealed mounting surface enables mounting without dead spaces; the impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning.

GN 75.6 waist shaped knobs have a compact and timeless design.

see also...

- Product Range [Hygienic Design](#)
- Sealing Rings GN 7600 ([Hygienic Design](#))

How to order	
<b>1</b> Handle diameter d <sub>1</sub>	
<b>2</b> Tapped hole d <sub>2</sub> (Threaded stud d <sub>3</sub> )	
<b>3</b> Type	
<b>4</b> Finish	

1 2 3 4  
**GN 75.6-25-M6-D-PL**