



**SS** Stainless Steel

**3 Type**

- D** with tapped
- E** with threaded stud

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Type D	<b>2</b> d <sub>3</sub> Type E	d <sub>4</sub>	d <sub>5</sub>	h	Length l	t min.
20 .79	M 5	M 5	14 .55	14.8 .58	24 .94	10 .39	7 .28
25 .98	M 6	M 6	16 .63	16.8 .66	29 1.14	12 .47	9 .35
32 1.26	M 8	M 8	18 .71	18.8 .74	37 1.46	14 .55	12 .47

**Specification**

- Stainless steel, European Standard No. 1.4404 (A4) (AISI 316 L)
  - Matte (Ra < 0.8 μm) **MT**
  - Polished (Ra < 0.8 μm) **PL**
- Sealing ring
  - Hydrogenated acrylonitrile butadiene rubber (H-NBR)
  - Blue
  - Temperature resistant -25 °C to +150 °C
  - Hardness 85±5 Shore A
  - FDA compliant
- **RoHS compliant**

**Information**

GN 75.6 waist shaped knobs are intended for use in hygiene areas. The sealed mounting surface enables mounting without dead spaces; the impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning.

GN 75.6 waist shaped knobs have a compact and timeless design.

How to order	
<b>1</b> d <sub>1</sub>	
<b>2</b> d <sub>2</sub>	
<b>3</b> Type	
<b>4</b> Finish	

**1 2 3 4**  
**75.6-25-M6-D-PL**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4