



**3 Type**  
**D** With tapped hole  
**E** With threaded stud

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Type D	<b>2</b> d <sub>3</sub> Type E	d <sub>4</sub>	h	Length l	t min.
17 .67	M 5	M 5	10 .39	14 .55	9 .35	7 .28
21 .83	M 6	M 6	12 .47	17 .67	10 .39	11 .43
25 .98	M 6	M 6	14 .55	21 .83	10 .39	11 .43
33 1.30	M 8	M 8	18 .71	29 1.14	14 .55	12 .47

**Specification**

- Plastic  
 Duroplast (Phenolic PF)  
 - Temperature resistant up to 230 °F (110 °C)  
 - Black, glossy finish
- Tapped insert (Type D)  
 Brass, molded-in
- Threaded stud (Type E)  
 Steel, zinc plated, blue passivated finish,  
 molded-in
- RoHS compliant

**Information**

GN 76 waist shaped knobs are widely used on push-pull type applications. The smooth shape gives the operator a comfortable grip.

see also...

- Ergostyle® Knurled Knobs EN 676 (Technopolymer Plastic, with Tapped Insert)
- Ergostyle® Knurled Knobs EN 676 (Technopolymer Plastic, with Threaded Stud)

How to order <b>GN 76-25-M6-D</b>	<b>1</b>	Handle diameter d <sub>1</sub>
	<b>2</b>	Thread d <sub>2</sub> (Threaded stud d <sub>3</sub> )
	<b>3</b>	Type