



ELESA original design ETH-EP / ETH-AN



Metric table

Dimensions in: millimeters - inches

d ₁	l ₁ ±1						a	b	d ₂	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄
28	300	400	500	600	700	-	62.5	28	8.5	54	68	20	26	19.5	20.3
1.10	11.81	15.75	19.69	23.62	27.56		2.46	1.10	.33	2.13	2.68	.79	1.02	.77	.80
35	300	400	500	600	700	1000	74	35	10.5	67	85.5	28	24.5	28.5	18.5
1.38	11.81	15.75	19.69	23.62	27.56	39.37	2.91	1.38	.41	2.64	3.37	1.10	.96	1.12	.73

* Not available from stock, requires a minimum order quantity

Specification

- Tube Ø 35 x 2
Aluminum
- **EN 767**
 - Graphite black powder coated
 - Metal effect, matte finish
 - Color of the end cap (shiny finish):
Black-gray, RAL 7021
Orange*, RAL 2004
Gray*, RAL 7035
Yellow*, RAL 1021
Blue*, RAL 5024
Red*, RAL 3000

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**

- **EN 767.1**
 - Anodized, natural color
 - Color of the end cap (shiny finish):
Black-gray, RAL 7021

- **DSG**

This information applies to both series:

- End pieces
Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 212 °F (100 °C)
 - Black-gray, matte finish, similar to RAL 7021
- **RoHS compliant**

On request

- Cleanline version
- Various metric and inch size fasteners and kit packaging

Information

EN 767 and EN 767.1 Ergostyle® tubular handles are highly resistant to wear, scratches and chemical agents. Avoid continuous and prolonged contact with boiling water or steam. Handle legs resistant to solvents, oils, greases and other chemical agents.

Special expansion-assembly system between tube and handle legs prevents rotation during operations. The mechanisms (screws/nuts/clamps) are shrouded by the removable end caps. On assembly the two end caps are inserted from above. To remove the end caps, a flat screw driver should be inserted in the provided recess to pry them out of their location. End caps are available in the different Ergostyle® colors which offers additional possibilities for a variety of color schemes.

Suggested tightening torque of the fasteners is 15 [Nm]. Two additional holding pins Ø 4 are included to keep the legs from twisting.

see also...

- **Product Range Ergostyle®**
- **Tubular Grip Handles GN 667 (Mounting from the Operator's Side)**

How to order (Powder coated tube) EN 767-35-700-DSG	1	Handle diameter d ₁
	2	Length l ₁
	3	Color of the end cap

How to order (Anodized tube) EN 767.1-35-500-DSG	1	Handle diameter d ₁
	2	Length l ₁
	3	Color of the end cap