



ELESA original design P.131

Metric table

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	d <sub>3</sub>	h	t <sub>1</sub> min.	t <sub>2</sub> ±0.5
35 1.38	M 8	19 .75	27 1.06	15 .59	3.5 .14
45 1.77	M 10	24 .94	34 1.34	20 .79	4 .16

Specification

- Plastic  
Duroplast (Phenolic PF)
  - Temperature resistant up to 230 °F (110 °C)
  - Black, shiny finish
  - Molded-in thread
- RoHS compliant

Information

EN 77 waist shaped knobs are great for use on push-pull type applications. The smooth shape gives the operator a comfortable grip.

On request

- With threaded stud

How to order <sup>1</sup> <sup>2</sup> <b>EN 77-35-M8</b>	<b>1</b> Handle diameter d <sub>1</sub>
	<b>2</b> Thread d <sub>2</sub>