



**SS** Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

2		3								
d <sub>1</sub>	NI	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub> ≈	l <sub>4</sub>	s	
KT		Thread								
16	-	M 6	10	13	41.5	12	4	15	8	
.63			.39	.51	1.63	.47	.16	.59	.31	
18	18	M 6	10	14.5	56	13	4	19	8	
.71	.71		.39	.57	2.20	.51	.16	.75	.31	
22	22	M 8	14	18.5	59	14	5.2	21	11	
.87	.87		.55	.73	2.32	.55	.20	.83	.43	
24	24	M 10	14	18.5	74	16	5.2	27	11	
.94	.94		.55	.73	2.91	.63	.20	1.06	.43	
25	-	M 10	16	20	84	16	5.5	30	13	
.98			.63	.79	3.31	.63	.22	1.18	.51	

**Specification**

- Plastic **KT**  
Technopolymer (Polyamide PA)  
- Temperature resistant up to 194 °F (90 °C)  
- Black, matte finish
- Stainless steel **NI**  
European Standard No. 1.4305 (AISI 303), fine turned
- Threaded spindle  
- Stainless steel  
European Standard No. 1.4305 (AISI 303)
- RoHS compliant

**Information**

GN 798.4 stepped cylindrical revolving handles are noted for their modern design, and the stepped shape provides the operator with a better grip.

see also...

- *Stepped Retractable Handles GN 798.5 (with Stainless Steel Locking Mechanism)*

<p>How to order</p> <p><b>GN 798.4-KT-16-M6</b></p>	1	Material
	2	Handle diameter d <sub>1</sub>
	3	Thread d <sub>2</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4