



ELESA original design EGH-SOFT



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Bore diameter	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> min.
22 .87	B 8	18 .71	85 3.35	60 2.36

**Specification**

- Plastic  
Technopolymer (Polypropylene PP)  
- Softline coating  
Elastomer (TPE) 70 shore A  
- Temperature resistant up to 176 °F (80 °C)  
- Black, matte finish
- Softline coating is chemically bonded with the plastic core
- RoHS compliant

**Information**

The EN 819 softline cylindrical handle does not require a thread on the shaft.  
During mounting, easy blows with a soft hammer are sufficient to drive the handle into place, the shaft end should be slightly rounded or chamfered (30°). The handle sits absolute vibration-tight.  
The semi-hard plastic material makes this handle very operator friendly.

see also...

- Product Range Ergostyle®
- Product Range Softline

<p>How to order</p> <p><sup>1</sup> <sup>2</sup></p> <p><b>EN 819-22-B8</b></p>	1 Handle diameter d <sub>1</sub>
	2 Bore diameter d <sub>2</sub>