



Inch table

Dimensions in: inches - millimeters

² d ₁	³ d ₂ Thread										t ₁
.75 19.1	10 x 32	10 x 24	-	-	-	-	-	-	-	-	.38 9.7
1.00 25.4	10 x 32	10 x 24	-	-	-	-	-	-	-	-	.38 9.7
1.00 25.4	1/4 x 20	1/4 x 28	5/16 x 18	5/16 x 24	3/8 x 16	-	-	-	-	-	.50 12.7
1.38 35.1	1/4 x 20	1/4 x 28	5/16 x 18	3/8 x 16	3/8 x 24	5/16 x 24	7/16 x 20	1/2 x 13	1/2 x 20	-	.63 16.0
1.88 47.8	3/8 x 16	3/8 x 24	5/8 x 11	1/2 x 13	1/2 x 20	5/8 x 18	-	-	-	-	.75 19.1

Specification

- Steel
Highly polished
- Brass
- Highly polished
- Corrosion resistant in water
- Tapped hole for mounting
- RoHS compliant



Information

Highly polished steel and brass balls turned from solid bar stock. Used on fixtures, machine tools, jigs and assemblies.

How to order

¹ ² ³
BK-MS-1.00-5/16X18

¹	Material
²	Handle diameter d₁
³	Thread d₂