



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$ Thread		$d_3$	$l_1$	$l_2$
17 .67	M 6	M 8	12 .47	45 1.77	8 .31
21 .83	M 8	M 10	16 .63	56 2.20	10 .39
23 .91	M 8	M 10	16 .63	61 2.40	10 .39
25 .98	M 8	M 10	18 .71	71 2.80	13 .51
28 1.10	M 10	M 12	20 .79	92 3.62	13 .51
29 1.14	M 10	M 12	20 .79	122 4.80	13 .51

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 300 °F (150 °C)  
- Black, shiny finish
- Threaded spindle  
Steel, zinc plated, with wrench flats
- RoHS compliant

**Information**

MCG cylindrical revolving handles can be used on most any device where a leverage for turning is required, i.e. handwheels or crank handles.

<p>How to order</p> <p><sup>1</sup> <sup>2</sup></p> <p><b>MCG-17-M6</b></p>	<b>1</b> Handle diameter $d_1$
	<b>2</b> Thread $d_2$