



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	d ₃	d ₄	l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	l ₇	l ₈
21 .83	M 5	7 .28	2.5 .10	57 2.24	50 1.97	7 .28	4 .16	8 .31	63 2.48	6.3 .25	27 1.06
23 .91	M 6	8 .31	2.5 .10	77 3.03	70 2.76	7 .28	4 .16	8 .31	84 3.31	7.5 .30	29 1.14
26 1.02	M 6	8 .31	2.5 .10	97 3.82	90 3.54	7 .28	4 .16	10 .39	107 4.21	7.5 .30	32 1.26

Specification

- Plastic
Nylon
 - Temperature resistant up to 212 °F (100 °C)
 - Black, matte finish
 - Revolving
- Retractable mechanism
Steel, zinc plated
- RoHS compliant

Information

Suitable for applications in which it is preferred that the revolving handle be folded away when in the rest position, and when a shorter protruding distance of the overall length is required. The handle can be folded in both directions.

On request

- For certain minimum quantities, other handle colors

<p>How to order</p> <p>¹ ²</p> <p>MRS-21-M5</p>	1 Handle diameter d ₁
	2 Thread d ₂