



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	d ₃	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	l ₇	l ₈
21 .83	M 5	17 .67	7 .28	2.5 .10	57 2.24	7 .28	8 .31	54.5 2.15	16.5 .65	14 .55	6.3 .25	4 .16
23 .91	M 6	19 .75	8 .31	2.5 .10	77 3.03	7 .28	8 .31	84.5 3.33	17.5 .69	18 .71	7.5 .30	4 .16
26 1.02	M 6	21 .83	8 .31	2.5 .10	97 3.82	7 .28	10 .39	96.5 3.80	19 .75	20 .79	7.5 .30	4 .16

Specification

- Plastic
Nylon
 - Temperature resistant up to 212 °F (100 °C)
 - Black, matte finish
 - Revolving
- Retractable mechanism
Steel, zinc plated
- RoHS compliant

Information

Suitable for applications in which it is preferred that the revolving handle be folded away when in the rest position, and when a shorter protruding distance of the overall length is required. The handle can be folded in both directions.

see also...

- Retractable Handles PGR (Nylon Plastic)
- Retractable Handles MGR (Phenolic Plastic)

Accessory

- ISO 2936 (DIN 911) hexagon keys available for installation

On request

- For certain minimum quantities, other handle colors

How to order ¹ ² MRS-21-M5	1 Handle diameter d ₁
	2 Thread d ₂