



Metric table

Dimensions in: millimeters - inches

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$ Bore diameter							$d_3$	$l_1$	$l_2$
23 .91	B 7	B 8	B 9	B 10	B 11	B 12	B 14	18 .71	60 2.36	55 2.17

Specification

- Plastic  
PVC
- Temperature resistant up to 60 °C (140 °F)
- Black
- Molded blind bore
- Push-fit mounting

• RoHS compliant

Information

MVP cylindrical handles offer a comfortable and elastic grip.

How to order <sup>1</sup> <sup>2</sup> <b>MVP-23-B7</b>	1	Handle diameter $d_1$
	2	Bore diameter $d_2$