



Metric table

Dimensions in: millimeters - *inches*

¹ d_1	² d_2 Bore diameter	d_3	l_1	l_2
20 .79	B 8	14 .55	37 1.46	34 1.34

Specification

- Plastic
PVC
- Temperature resistant up to 140 °F (60 °C)
- Black
- Molded blind bore
- Push-fit mounting
- **RoHS compliant**

Information

The MVP-CON tapered handle offers a comfortable and elastic grip.

<p>How to order</p> <p>¹ ²</p> <p>MVP-CON-20-B8</p>	1 Handle diameter d_1
	2 Bore diameter d_2