



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	d ₄	l ₁	l ₂	l ₃	A/F
41 1.61	M 8	13 .51	15 .59	54 2.13	12 .47	4 .16
41 1.61	M 10	13 .51	17 .67	54 2.13	12 .47	5 .20
47 1.85	M 8	14 .55	15 .59	58 2.28	12 .47	4 .16
47 1.85	M 10	14 .55	17 .67	58 2.28	12 .47	5 .20
60 2.36	M 8	14 .55	15 .59	71 2.80	12 .47	4 .16
60 2.36	M 10	14 .55	17 .67	71 2.80	12 .47	5 .20

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 300 °F (150 °C)
- Black, shiny finish
- Spindle
Steel, zinc plated
- RoHS compliant

Information

PB/GE revolving ball knobs can be utilized instead of revolving handles, e.g. with handwheels or crank handles.

On request

- DIN 911 hexagon keys available for installation

<p>How to order</p> <p>¹ ²</p> <p>PB-GE-41-M8</p>	1 Handle diameter d ₁
	2 Thread d ₂