



Inch table

4 Type

- C With tapped hole (no insert)
- E With tapped insert

Dimensions in: inches - millimeters

d ₁		d ₂				d ₃ ≈	h	t
Type E	Type C	Thread						
.75 19.1	-	6 x 32	8 x 32	10 x 24	10 x 32	.38 9.7	.70 17.8	.31 7.9
.75 19.1	-	1/4 x 20	-	-	-	.38 9.7	.70 17.8	.38 9.7
1.00 25.4	-	10 x 32	-	-	-	.50 12.7	.97 24.6	.31 7.9
1.00 25.4	-	1/4 x 20	1/4 x 28	5/16 x 18	5/16 x 24	.50 12.7	.97 24.6	.44 11.2
1.00 25.4	-	3/8 x 16	3/8 x 24	-	-	.50 12.7	.97 24.6	.50 12.7
1.19 30.2	-	1/4 x 20	5/16 x 18	5/16 x 24	-	.56 14.2	1.13 28.7	.44 11.2
1.19 30.2	-	3/8 x 16	3/8 x 24	-	-	.56 14.2	1.13 28.7	.50 12.7
1.38 35.1	-	1/4 x 20*	5/16 x 18	5/16 x 24	-	.63 16.0	1.30 33.0	.44 11.2
1.38 35.1	-	3/8 x 16	3/8 x 24	7/16 x 20	-	.63 16.0	1.30 33.0	.50 12.7
1.38 35.1	-	1/2 x 13	1/2 x 20	-	-	.63 16.0	1.30 33.0	.63 16.0
1.50 38.1	-	5/16 x 18	3/8 x 16	-	-	.63 16.0	1.49 37.8	.50 12.7
-	1.50 38.1	1/4 x 20	-	-	-	.63 16.0	1.49 37.8	.63 16.0
-	1.50 38.1	1/2 x 13	-	-	-	.63 16.0	1.49 37.8	.88 22.4
1.63 41.4	-	5/16 x 18	5/16 x 24	-	-	.69 17.5	1.58 40.1	.44 11.2
1.63 41.4	-	3/8 x 16	3/8 x 24	7/16 x 20	-	.69 17.5	1.58 40.1	.50 12.7
1.63 41.4	-	1/2 x 13	1/2 x 20	-	-	.69 17.5	1.58 40.1	.63 16.0
1.88 47.8	-	3/8 x 16	3/8 x 24	-	-	.75 19.1	1.80 45.7	.50 12.7
1.88 47.8	-	1/2 x 13	1/2 x 20	-	-	.75 19.1	1.80 45.7	.63 16.0
-	1.88 47.8	3/8 x 16	3/8 x 24	-	-	.75 19.1	1.80 45.7	.63 16.0
-	1.88 47.8	5/8 x 18	-	-	-	.75 19.1	1.80 45.7	.88 22.4

Specification



- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 300 °F (150 °C)
- Black, glossy finish
- Tapped insert
Brass, molded-in
- Plain thread
Molded-in
- RoHS compliant

KU

Information

PBH plastic ball knobs can be used on machine tools, jigs, fixtures, and a variety of other equipment.

On request

- Other colors

<p>How to order</p> <p>1 2 3 4</p> <p>PBH-KU-0.75-6X32-E</p>	1	Material
	2	Ball diameter d ₁
	3	Thread d ₂
	4	Type