



Inch table

Dimensions in: inches - millimeters

Length <sup>1</sup> l	d <sub>1</sub> Thread <sup>2</sup>			d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	t
2.25 57.2	1/4 x 20	5/16 x 18	3/8 x 16	.75 19.1	1.44 36.6	.69 17.5	.50 12.7

Specification

- Plastic  
Nylon  
- Temperature resistant up to 230 °F (110 °C)  
- Black, matte finish
- Tapped insert  
Brass, molded-in
- RoHS compliant

Information

TBK T-bar knobs are a great choice for pull-action applications due to their ergonomically rounded shape.

On request

- Additional thread sizes
- Special stud assemblies (glued into place)

<p>How to order</p> <p><sup>1</sup> <sup>2</sup></p> <p>TBK-2.25-3/8X16</p>	1 Handle length l
	2 Thread d <sub>1</sub>