



Inch table

Dimensions in: inches - millimeters

Length 1	2 d_1 Thread		Steel	d_2	h_1	h_2	t
	Brass						
2.50 63.5	1/4 x 20	5/16 x 18	-	.75 19.1	1.13 28.7	.50 12.7	.50 12.7
3.50 88.9	3/8 x 16	-	-	.94 23.9	1.13 28.7	.50 12.7	.50 12.7
3.50 88.9	-	-	1/2 x 13	.94 23.9	1.13 28.7	.30 7.6	.88 22.4

Specification

- Plastic
Polypropylene
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Tapped insert
 - Molded-in
 - Brass **MS**
 - Steel, zinc plated **ST**
- RoHS compliant

Information

The wide surface area of the TH T-bar knobs allow for positive low profile clamping.

On request

- Special stud assemblies (glued into place)

How to order 1 2 3 TH-2.50-5/16X18-MS	1 Handle length l
	2 Thread d_1
	3 Material