



Metric table

Dimensions in: millimeters - inches

| Length ¹ l | d ² Thread | h ₁ | h ₂ | b | t |
|-----------------------|-----------------------|----------------|----------------|-----------|-----------|
| 57 2.24 | M 6 | 30 1.18 | 16 .63 | 15 .59 | 13 .51 |
| 57 2.24 | M 8 | 30 1.18 | 16 .63 | 15 .59 | 15 .59 |

Specification

- Plastic
Nylon
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
 - Glass filled
 - Molded-in thread

• RoHS compliant

On request

- Special stud assemblies (glued into place)

Information

The wide surface area of TIR T-bar knobs allow for positive low profile clamping.
Resistant to solvents, oils, grease and other chemical agents.

| | |
|---|-------------------|
| How to order ¹ ² TIR-57-M6 | 1 Handle length l |
| | 2 Thread d |