



Metric table

Dimensions in: millimeters - inches

Length ¹ l	² d Thread	h_1	h_2	b	t
57 2.24	M 6	30 1.18	16 .63	15 .59	13 .51
57 2.24	M 8	30 1.18	16 .63	15 .59	15 .59

Specification

- Plastic
Nylon
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
 - Glass filled
 - Molded-in thread
- RoHS compliant

On request

- Special stud assemblies (glued into place)

Information

The wide surface area of TIR T-bar knobs allow for positive low profile clamping. Resistant to solvents, oils, grease and other chemical agents.

see also...

- T-Handles (Aluminum)

How to order ¹ ² TIR-57-M6	1 Handle length l
	2 Thread d

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

