



3 Type

- A Without handle
- D With revolving handle

Metric table

Dimensions in: millimeters - inches

1 d_1	2 d_2 Pilot hole	d_3	d_4	b	l_1	l_2	l_3	l_4	l_5	d_5
100 3.94	P 4	24 .94	17 .67	15 .59	33 1.30	11 .43	40 1.57	45 1.77	85 3.35	M 8
125 4.92	P 6	24 .94	23 .91	17 .67	36 1.42	13 .51	46 1.81	61 2.40	107 4.21	M 8
150 5.91	P 6	32 1.26	25 .98	20 .79	37 1.46	13 .51	49 1.93	71 2.80	120 4.72	M 10
175 6.89	P 6	40 1.57	25 .98	22 .87	41 1.61	16 .63	56 2.20	71 2.80	127 5.00	M 10
200 7.87	P 6	40 1.57	28 1.10	24 .94	44 1.73	16 .63	61 2.40	92 3.62	153 6.02	M 10
250 9.84	P 6	48 1.89	28 1.10	28 1.10	49 1.93	17 .67	72 2.83	92 3.62	164 6.46	M 10
300 11.81	P 6	58 2.28	28 1.10	34 1.34	54 2.13	18 .71	78 3.07	92 3.62	170 6.69	M 10

Specification

- Phenolic plastic
 - Glass fiber reinforced
 - Temperature resistant up to 300 °F (150 °C)
 - Black
- Hub bushing
 - Steel, zinc plated, molded-in
- Revolving handles
 - Phenolic plastic
 - Black, matte finish
 - Rim
 - Steel, zinc plated
- Both dimensions, inch and metric, are interchangeable
- RoHS compliant

Information

VRAF three spoked handwheels are distinguished by modern design. An excellent choice for light-medium duty applications.

No mounting hole in handwheel rim for handwheel without handle Handle shipped loose; mounting of handle is required.

On request

- Special inch and metric bores
- Other modifications such as keyways, set screw holes, etc.

How to order VRAF-100-P4-A	1	Handwheel diameter d_1
	2	Pilot hole d_2
	3	Type