



SS Stainless Steel

4 Type

- C With tapped hole
- K With bore H7

Metric table

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub> Type C	d <sub>3</sub> H7 Type K	d <sub>4</sub>	h	t <sub>1</sub> min.	t <sub>2</sub> min.
16 .63	M 4	B 6	8 .31	15 .59	7 .28	9 .35
20 .79	M 5	B 8	12 .47	18 .71	9 .35	11 .43
25 .98	M 6	B 10	15 .59	22.5 .89	11 .43	14 .55
32 1.26	M 8	B 12	18 .71	29 1.14	14.5 .57	17 .67
40 1.57	M 10	B 16	22 .87	37 1.46	18 .71	22 .87
50 1.97	M 12*	B 20	27 1.06	46 1.81	21 .83	28 1.10

\* This size is only available in steel and aluminum.

Specification

- Steel **ST**  
Turned and polished
- Aluminum **AL**  
Turned and polished
- Stainless steel **NI**  
European Standard No. 1.4305 (AISI 303)  
Matte shot-blasted finish
- RoHS compliant

Information

Metal ball knobs, instead of plastic ball knobs, are suitable for heavy duty application uses. The stainless steel option is an excellent choice for corrosion-free applications.

On request

- For certain minimum quantities, steel ball knobs can also be supplied plated.

How to order

**DIN 319-NI-40-M10-C**

1	Material
2	Ball diameter d <sub>1</sub>
3	Thread d <sub>2</sub> (Bore diameter d <sub>3</sub> )
4	Type