



ELESA original design 1.149

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	³ l ₁	d ₃	l ₂ min.	l ₃ ±0.5	l ₄ ≈
34 1.34	M 10	67 2.64	19 .75	40 1.57	8 .31	24 .94
34 1.34	M 10	86 3.39	20 .79	48 1.89	7 .28	25 .98

Specification

- Plastic
Duroplast (Phenolic PF)
 - Temperature resistant up to 230 °F (110 °C)
 - Black, shiny finish
 - Molded-in thread

• RoHS compliant

Information

When using EN 219 tapered knobs, make sure that the threaded end of the shaft is long enough and seats flush inside the threaded hole of the handle, otherwise the plastic may break under excessive stress.

How to order ¹ ² ³ EN 219-34-M10-67	1 Handle diameter d ₁
	2 Thread d ₂
	3 Handle length l ₁