



**SS** Stainless Steel

**4 Type**

- C** with tapped hole
- K** with bore H7

**Metric table**

Dimensions in: millimeters - inches

<b>2</b> $d_1$ Ball diameter	<b>3</b> $d_2$ Type C Thread	<b>3</b> $d_3$ H7 Type K Bore diameter	$d_4$	$h$	$t_1$ min.	$t_2$ min.
16 .63	M 4	B 6	8 .31	15 .59	7 .28	9 .35
20 .79	M 5	B 8	12 .47	18 .71	9 .35	11 .43
25 .98	M 6	B 10	15 .59	22.5 .89	11 .43	14 .55
32 1.26	M 8	B 12	18 .71	29 1.14	14.5 .57	17 .67
40 1.57	M 10	B 16	22 .87	37 1.46	18 .71	22 .87
50 1.97	M 12*	B 20	27 1.06	46 1.81	21 .83	28 1.10

\* This size is only available in steel and aluminum.

**Specification**

- Steel **ST**  
Turned and polished
- Aluminum **AL**  
Turned and polished
- Stainless steel **NI**  
European Standard No. 1.4305 (AISI 303)  
Matte shot-blasted finish
- RoHS compliant

**Information**

Metal ball knobs, instead of plastic ball knobs, are suitable for heavy duty application uses. The stainless steel option is an excellent choice for corrosion-free applications.

**On request**

- For certain minimum quantities, steel ball knobs can also be supplied plated.

How to order

**DIN 319-NI-40-M10-C**

<b>1</b>	<b>Material</b>
<b>2</b>	<b>Ball diameter <math>d_1</math></b>
<b>3</b>	<b>Thread <math>d_2</math> (Bore diameter <math>d_3</math>)</b>
<b>4</b>	<b>Type</b>