



- 2** Bore code
B Without keyway
V With square

Specification

- Pressed steel
Powder coated
Black, smooth finish
- Hub welded to body
Steel
- RoHS compliant

Information

The hub lengths of the pressed Stainless Steel Handwheels, GN 227, conform to DIN 950.
 GN 227.1 pressed steel handwheels are renowned for their high mechanical strength. They are not affected by shock and knocks. They are of an attractive design and shape at a reasonable cost.

see also...

- Countersunk Washers GN 184 (for Axial Fixing)

On request

- Other modifications such as special through bores, square broached holes larger than listed, keyways, set screw holes and cross holes
- With Revolving Handle

How to order	1 Handwheel diameter d_1
1 2 3 4	2 Bore code
GN 227.1-125-B1/2-SW	3 d_2
	4 Color

How to order	1 Handwheel diameter d_1
1 2 3 4	2 Bore code
GN 227.1-125-V11-SW	3 d_2
	4 Color

Inch table

Dimensions in: inches - *millimeters*

d₁	d₂ +0.002 Bore	s +0.002 Square	b	d₃	l₁	l₂ ≈	No. of spokes	Thickness of pressed stainless steel
4.92 125	1/2	V 1/2	.71 18	1.18 30	.71 18	1.14 29	3	.06 1.5
6.30 160	1/2	V 1/2	.87 22	1.18 30	.79 20	1.46 37	4	.06 1.5
7.87 200	5/8	V 5/8	.87 22	1.57 40	.94 24	1.81 46	4	.10 2.5
9.84 250	3/4	V 3/4	1.18 30	1.77 45	1.10 28	2.05 52	5	.10 2.5
12.40 315	3/4	V 3/4	1.38 35	2.17 55	1.30 33	2.52 64	5	.10 2.5
15.75 400	1.00	V 1.00	1.57 40	2.56 65	1.50 38	3.23 82	5	.12 3

Metric table

Dimensions in: millimeters - *inches*

d₁	d₂ H9 Bore	s H11 Square	b	d₃	l₁	l₂ ≈	No. of spokes	Thickness of pressed stainless steel
125 4.92	11	V 11	18 .71	30 1.18	18 .71	29 1.14	3	1.5 .06
160 6.30	12	V 12	22 .87	30 1.18	20 .79	37 1.46	4	1.5 .06
200 7.87	14	V 14	22 .87	40 1.57	24 .94	46 1.81	4	2.5 .10
250 9.84	17	V 17	30 1.18	45 1.77	28 1.10	52 2.05	5	2.5 .10
315 12.40	19	V 19	35 1.38	55 2.17	33 1.30	64 2.52	5	2.5 .10
400 15.75	24	V 24	40 1.57	65 2.56	38 1.50	82 3.23	5	3 .12