



SS Stainless Steel

3 Type

- A DIN 319 ball knob
- D EN 719 domed gear lever knob
- E EN 519 cylindrical handle

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 l ₁			d ₂ Thread	d ₃	d ₄	d ₅	l ₂	l ₃	l ₄	l ₅
8 .31	63 2.48	80 3.15	100 3.94	M 6	20 .79	20 .79	18 .71	9 .35	18 .71	32 1.26	40 1.57
10 .39	80 3.15	100 3.94	125 4.92	M 8	25 .98	26 1.02	21 .83	11 .43	22.5 .89	42 1.65	50 1.97
12 .47	100 3.94	125 4.92	160 6.30	M 10	32 1.26	33 1.30	23 .91	14 .55	29 1.14	55 2.17	65 2.56
14 .55	125 4.92	160 6.30	200 7.87	M 12	35 1.38	33 1.30	26 1.02	16 .63	32.5 1.28	55 2.17	80 3.15
16 .63	160 6.30	200 7.87	250 9.84	M 14	40 1.57	38 1.50	28 1.10	18 .71	37 1.46	69 2.72	90 3.54

Specification

- Shaft
 - Steel, zinc plated, blue passivated finish **ZB**
 - Stainless steel **NI**
 - European Standard No. 1.4305 (AISI 303), matte shot-blasted finish
- Knobs
 - Plastic
 - Duroplast (Phenolic PF)
 - Temperature resistant up to 300 °F (150 °C)
 - Black, glossy finish
 - Screwed-on
- Ball Knobs DIN 319
- Domed Gear Lever Knobs EN 719
- Cylindrical Handles EN 519
- RoHS compliant

On request

- For certain minimum quantities, special threads and shaft lengths

Information

GN 310 gear lever handles are highly universal options for movement and operation. Used for actuating the material flow through hydraulic valves via the lever handle or, used as control levers for on / off, start / stop applications where the lever handle is attached to set collars, split hubs, or eccentric cams, are example uses of these standard parts.

The choice of knobs can be made dependent on their function and/or their modern design.

How to order (Steel)	1 Handle diameter d ₁
1 2 3 4 GN 310-10-125-E-ZB	2 Handle length l ₁
	3 Type
	4 Material

How to order (Stainless steel)	1 Handle diameter d ₁
1 2 3 4 GN 310-12-100-A-NI	2 Handle length l ₁
	3 Type
	4 Material

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

