



ELESA original design I.580 N

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Bore diameter		d ₃	l ₁	l ₂ min.
18 .71	B 8	-	15 .59	40 1.57	28 1.10
21 .83	B 10	-	17 .67	50 1.97	35 1.38
23 .91	B 10	B 12	19 .75	65 2.56	45 1.77
26 1.02	B 12	B 14	21 .83	80 3.15	50 1.97
28 1.10	B 15	B 16	22 .87	90 3.54	60 2.36

Specification

- Plastic
Technopolymer (Polypropylene PP)
 - Shock resistant
 - Temperature resistant up to 175 °F (80 °C)
 - Black, matte finish
- RoHS compliant

Information

The use of EN 519.1 cylindrical handles eliminates the need for a thread on the shaft.

These cylindrical handles are assembled onto a shaft using a plastic mallet. During mounting, easy blows with a soft hammer are sufficient to drive the handle into place. The shaft end should be slightly rounded or chamfered (30°).

In order to increase the elasticity, the bore is equipped with longitudinal ribs that provide a very firm seating of the handle onto the shaft.

These handles fit absolutely vibration-tight.

see also...

- Cylindrical Handles EN 819 (Press-On Type)

How to order ¹ ² EN 519.1-18-B8	1	Handle diameter d ₁
	2	Bore diameter d ₂