



ELESA original design I.680 SOFT



Metric table

Dimensions in: millimeters - inches

¹ d ₁ +0.5 Handle diameter	² d ₂ Thread	d ₃	l ₁	l ₂ min.	l ₃
24 .94	M 8	20.5 .81	65 2.56	30 1.18	7 .28
24 .94	M 10	20.5 .81	65 2.56	40 1.57	7 .28
26 1.02	M 8	21 .83	80 3.15	40 1.57	7 .28
26 1.02	M 10	21 .83	80 3.15	55 2.17	7 .28
26 1.02	M 12	21 .83	80 3.15	55 2.17	7 .28
28 1.10	M 10	22 .87	90 3.54	56 2.20	7 .28
28 1.10	M 12	22 .87	90 3.54	58 2.28	10 .39

Specification

- Plastic
Technopolymer (Propylene PP)
 - Softline coating
Elastomer (TPE) 70 shore A
 - Chemically bonded with the plastic core
 - With FDA admission
 - Temperature resistant up to 175 °F (80 °C)
 - Black, matte finish
 - Molded-in thread

- RoHS compliant

Information

The softline coating of EN 519.6 cylindrical handles makes them ergonomically operator friendly. The soft, antislip contact surface is very user friendly. It improves the contact between a damp (perspiration) or dry hand, or an oily surface, whether in a cold or hot environment.

see also...

- Product Range Softline
- Cylindrical Handles EN 519 (Phenolic plastic, with molded-in thread)
- Cylindrical Handles EN 519.1 (Technopolymer plastic, press-on type)

How to order ¹ ² EN 519.6-24-M8	1 Handle diameter d ₁
	2 Thread d ₂