



ELESA original design IH.N

Metric table

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Bore diameter	d <sub>3</sub>	d <sub>4</sub> Symbol Ø	h	t
27 1.06	B 8	15 .59	20 .79	42 1.65	25 .98
32 1.26	B 10	18 .71	25 .98	49 1.93	25 .98

Specification

- Plastic  
Technopolymer (Polyamide PA)  
- Temperature resistant up to 194 °F (90 °C)  
- Black, shiny finish
- Transparent sight cap with magnifying effect
- RoHS compliant

Accessory

- EN 517.1 positioning symbols (printed on self-adhesive foil, color silver-gray / black)

Information

EN 518 tapered knobs do not require a thread at the shaft. During mounting, easy blows with a soft hammer are sufficient to drive the knob into place, the shaft end should be slightly rounded or chamfered (30°). The knobs sit absolute vibration-tight.

The transparent sight glass allows symbols to be placed underneath.

Once the knob is mounted on the shaft, the symbol is placed into the recess of the separately supplied sight glass and driven home with a soft hammer.

The symbol is fully protected from dirt and liquid by the tight connection between the sight glass and the knob.

EN 517.1 positioning symbols are to be ordered separately.

see also...

- Positioning Symbols EN 517.1
- Softline Mushroom Shaped Knobs EN 718.1 (Press-On Type)

How to order <sup>1</sup> <sup>2</sup> <b>EN 518-32-B10</b>	1 Handle diameter d <sub>1</sub>
	2 Bore diameter d <sub>2</sub>