



ELESA original design 1.280 p

Metric table

Dimensions in: millimeters - inches

| ¹ d_1 | ² d_2 Thread | d_3 | l_1 | l_2 |
|-----------------------|---------------------------------|-----------|-------------|-----------|
| 18 .71 | M 6 | 15 .59 | 40 1.57 | 16 .63 |
| 21 .83 | M 8 | 17 .67 | 50 1.97 | 16 .63 |
| 23 .91 | M 10 | 19 .75 | 65 2.56 | 16 .63 |
| 26 1.02 | M 10 | 21 .83 | 80 3.15 | 16 .63 |
| 28 1.10 | M 12 | 22 .87 | 90 3.54 | 16 .63 |
| 31 1.22 | M 12 | 25 .98 | 102 4.02 | 16 .63 |

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- Spindle
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

EN 539 fixed cylindrical handles can equally well be used to replace ball knobs on operating / gear lever handles. In that case the operating end of the lever handle will need to have a tapped hole for mounting the EN 539 fixed cylindrical handle.

The threaded spindle is deeply embedded in the handle which greatly increases the strength of the plastic body.

see also...

- Revolving Handles GN 598

| | |
|---|--------------------------------|
| <p>How to order</p> <p>¹ ²</p> <p>EN 539-21-M8</p> | 1 Handle diameter d_1 |
| | 2 Thread d_2 |