



ELESA original design L.652 p

Inch table

Dimensions in: inches - millimeters

¹ I ₁ Nominal dimension	Actual dimension	² d Thread	³ l ₂ Stud length	h ₁	h ₂	s Square
1.57 40	1.61 41	1/4 x 20	.75 19	1.18 30	.79 20	.51 13
2.17 55	2.22 56.5	5/16 x 18	.75 19	1.30 33	.87 22	.59 15
2.64 67	2.70 68.5	5/16 x 18	1.00 25.4	1.46 37	.98 25	.65 16.5
3.15 80	3.23 82	3/8 x 16	1.25 31.7	1.61 41	1.02 26	.79 20
3.66 93	3.70 94	1/2 x 13	1.25 31.7	1.77 45	1.12 28.5	.83 21

Metric table

Dimensions in: millimeters - inches

¹ I ₁ Nominal dimension	Actual dimension	² d Thread	³ l ₂ Stud length	h ₁	h ₂	s Square
40 1.57	41 1.61	M 5	16 .63	20 .79	-	30 1.18
40 1.57	41 1.61	M 6	20 .79	25 .98	-	30 1.18
55 2.17	56.5 2.22	M 6	20 .79	25 .98	-	33 1.30
55 2.17	56.5 2.22	M 8	20 .79	25 .98	-	33 1.30
67 2.64	68.5 2.70	M 8	20 .79	25 .98	30 1.18	37 1.46
67 2.64	68.5 2.70	M 10	20 .79	30 1.18	-	37 1.46
80 3.15	82 3.23	M 10	20 .79	30 1.18	-	41 1.61
93 3.66	94 3.70	M 12	30 1.18	-	-	45 1.77

Specification

- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Threaded stud
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

EN 563.1 T-handles can be used either as operating handles or for clamping purposes, providing high clamping force.

see also...

- T-Handles GN 563.2 (Aluminum)

How to order	¹ Handle length I ₁
EN 563.1-40-1/4X20-19	² Thread d
	³ Stud length l ₂